



EcoFIX TCS262

TCS262 4xTL5-13W/840 EB C6

4, TL5, 13 W, 840 neutral white, Electronic, High-gloss optic double parabolic closed

EcoFIX is a modular luminaire for TL5 tubular fluorescent lamps. At only 55 mm in height, it is especially designed for ceilings of 625 mm. It is available in very high-performance recessed versions for two, three or four TL5 lamps of 14, 25, 28, 50 or 54 W with compact dimensions which integrate better into the environment. With very high-performance and efficient C6 optics, it offers excellent light control thanks to its innovative optical system with omni-directional luminance control (OLC), which makes maximum use of the light emitted by the lamp without creating any glare.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	4
Light source color	840 neutral white
Optic type	High-gloss optic double parabolic closed
Operating and Electrical	
Power Consumption	13 W

Product Data	
Order product name	TCS262 4xTL5-13W/840 EB C6
Full product name	TCS262 4xTL5-13W/840 EB C6
Full product code	919106029172
Order code	919106029172
Material Nr. (12NC)	919106029172
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400817794
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400817794

EcoFIX TCS262

Dimensional drawing

