



# EcoBATTEN

## TMS942 2xTL5-54W/840 EB WR

2, TL5, 54 W, 840 neutral white, Electronic, White reflector without louver

EcoBATTEN is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25, 28, 50 or 54 W TL5 fluorescent tube lamps and can be used at heights of between 2.5 and 12 m. Available in five versions with high performance.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	White reflector without louver
Operating and Electrical	
Power Consumption	54 W

Product Data	
Order product name	TMS942 2xTL5-54W/840 EB WR
Full product name	TMS942 2xTL5-54W/840 EB WR
Full product code	919106029321
Order code	919106029321
Material Nr. (12NC)	919106029321
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

Dimensões em mm:

