



# EcoBATTEN

## TMS943 2xTL5-54W/840 EB R-H

2, TL5, 54 W, 840 neutral white, Electronic, Reflector high reflectance

EcoBATTEN is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25, 28, 50 or 54 W TL5 fluorescent tube lamps and can be used at heights of between 2.5 and 12 m. Available in five versions with high performance.

### Product data

| General Information      |                            |
|--------------------------|----------------------------|
| Lamp family code         | TL5 [TL5]                  |
| Gear                     | EB [Electronic]            |
| Light Technical          |                            |
| Number of light sources  | 2                          |
| Light source color       | 840 neutral white          |
| Optic type               | Reflector high reflectance |
| Operating and Electrical |                            |
| Power Consumption        | 54 W                       |

| Product Data                    |                             |
|---------------------------------|-----------------------------|
| Order product name              | TMS943 2xTL5-54W/840 EB R-H |
| Full product name               | TMS943 2xTL5-54W/840 EB R-H |
| Full product code               | 919106029361                |
| Order code                      | 919106029361                |
| Material Nr. (12NC)             | 919106029361                |
| Numerator - Quantity Per Pack   | 1                           |
| Numerator - Packs per outer box | 1                           |

## Dimensional drawing

Dimensões em mm:

