



# EcoBATTEN

## TMS940 2xTL5-28W/840 EB WR PC

2, TL5, 28 W, 840 neutral white, Electronic, White reflector without louver, Polycarbonate bowl/cover

EcoBATTEN is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25, 28, 50 or 54 W TL5 fluorescent tube lamps and can be used at heights of between 2.5 and 12 m. Available in five versions with high performance.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	White reflector without louver
Optical cover type	Polycarbonate bowl/cover
Operating and Electrical	
Power Consumption	28 W

Product Data	
Order product name	TMS940 2xTL5-28W/840 EB WR PC
Full product name	TMS940 2xTL5-28W/840 EB WR PC
Full product code	919106029391
Order code	919106029391
Material Nr. (12NC)	919106029391
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

Dimensões em mm:

