



EcoBAY TPK377

TPK377 4xTL5-54W/840 EB C-H

4, TL5, 54 W, Electronic, High-gloss high reflectance

EcoBAY is a range of contemporary single luminaires with an MIRO4 aluminum reflector, which combines the advantages of TL5 HO fluorescent lamps with high color rendering index (CRI), high luminous flux, and the flexibility to mount traditional HID luminaires. EcoBAY was developed as an option to replace the luminaires that use discharge lamps, for areas with a height of 6 to 9 meters. They are available for four TL5 HO lamps of 50 and 54 W; open and closed versions with polycarbonate diffuser. EcoBAY luminaires are very compact and come fitted with lamps and ballasts. With EcoBAY the owner also reduces energy consumption and maintenance costs.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	4
Light source color	840 neutral white
Optic type	High-gloss high reflectance
Operating and Electrical	
Power Consumption	54 W

Product Data	
Order product name	TPK377 4xTL5-54W/840 EB C-H
Full product name	TPK377 4xTL5-54W/840 EB C-H
Full product code	919106029851
Order code	919106029851
Material Nr. (12NC)	919106029851
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

EcoBAY TPK377

Dimensional drawing

Dimensões em mm:

