



Europa

FBS672 2XPL-C/4P26W/840 EB GF WH

2, MASTER PL-C 4 Pin, 26 W, 840 neutral white, Electronic,
Glass frosted, White

The Europa range offers high performance and an attractive design. It offers an effective solution for various types of commercial establishments since it optimizes the use of electrical energy whilst also ensuring visual comfort. The downlighters of the Europa range create a pleasant and inviting atmosphere, making the lighting an excellent way to promote sales.

Product data

| General Information | |
|--------------------------|-----------------------------|
| Lamp family code | PL-C/4P [MASTER PL-C 4 Pin] |
| Gear | EB [Electronic] |
| Light Technical | |
| Number of light sources | 2 |
| Light source color | 840 neutral white |
| Optical cover type | Glass frosted |
| Operating and Electrical | |
| Input Voltage | 220 V |
| Line Frequency | 60 Hz |
| Input Frequency | 60 Hz |
| Power Consumption | 26 W |

| Mechanical and Housing | |
|---------------------------------|----------------------------------|
| Housing Color | White |
| Product Data | |
| Order product name | FBS672 2XPL-C/4P26W/840 EB GF WH |
| Full product name | FBS672 2XPL-C/4P26W/840 EB GF WH |
| Full product code | 919106031101 |
| Order code | 919106031101 |
| Material Nr. (12NC) | 919106031101 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

Dimensional drawing

Torino / Milano

