



EcoBAY TPK377

TPK377 4xTL5-50W/840 HFD C-H

4, TL5, 50 W, HF DALI, High-gloss high reflectance

EcoBAY is a range of contemporary single luminaires with an MIRO4 aluminum reflector, which combines the advantages of TL5 HO fluorescent lamps with high color rendering index (CRI), high luminous flux, and the flexibility to mount traditional HID luminaires. EcoBAY was developed as an option to replace the luminaires that use discharge lamps, for areas with a height of 6 to 9 meters. They are available for four TL5 HO lamps of 50 and 54 W; open and closed versions with polycarbonate diffuser. EcoBAY luminaires are very compact and come fitted with lamps and ballasts. With EcoBAY the owner also reduces energy consumption and maintenance costs.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFD [HF DALI]
Light Technical	
Number of light sources	4
Light source color	840 neutral white
Optic type	High-gloss high reflectance
Operating and Electrical	
Power Consumption	50 W

Product Data	
Order product name	TPK377 4xTL5-50W/840 HFD C-H
Full product name	TPK377 4xTL5-50W/840 HFD C-H
Full product code	919106031439
Order code	919106031439
Material Nr. (12NC)	919106031439
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400818845
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400818845

EcoBAY TPK377

Dimensional drawing

Dimensões em mm:

