



EcoBAY TPK377

TPK377 4xTL5-50W/840 EB C-H PC

4, TL5, 50 W, Electronic, High-gloss high reflectance, Polycarbonate bowl/cover

EcoBAY is a range of contemporary single luminaires with an MRO4 aluminum reflector, which combines the advantages of TL5 HO fluorescent lamps with high color rendering index (CRI), high luminous flux, and the flexibility to mount traditional HID luminaires. EcoBAY was developed as an option to replace the luminaires that use discharge lamps, for areas with a height of 6 to 9 meters. They are available for four TL5 HO lamps of 50 and 54 W; open and closed versions with polycarbonate diffuser. EcoBAY luminaires are very compact and come fitted with lamps and ballasts. With EcoBAY the owner also reduces energy consumption and maintenance costs.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	4
Light source color	840 neutral white
Optic type	High-gloss high reflectance
Optical cover type	Polycarbonate bowl/cover
Operating and Electrical	
Power Consumption	50 W

Product Data	
Order product name	TPK377 4xTL5-50W/840 EB C-H PC
Full product name	TPK377 4xTL5-50W/840 EB C-H PC
Full product code	919106031441
Order code	919106031441
Material Nr. (12NC)	919106031441
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

EcoBAY TPK377

Dimensional drawing

Dimensões em mm:

