



EcoBATTEN

TMS940 2xTL5-50W/840 EB WR PC

2, TL5, 50 W, 840 neutral white, Electronic, White reflector without louver, Polycarbonate bowl/cover

EcoBATTEN is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25, 28, 50 or 54 W TL5 fluorescent tube lamps and can be used at heights of between 2.5 and 12 m. Available in five versions with high performance.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	White reflector without louver
Optical cover type	Polycarbonate bowl/cover
Operating and Electrical	
Power Consumption	50 W

Product Data	
Order product name	TMS940 2xTL5-50W/840 EB WR PC
Full product name	TMS940 2xTL5-50W/840 EB WR PC
Full product code	919106031451
Order code	919106031451
Material Nr. (12NC)	919106031451
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400001742
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400001742

Dimensional drawing

Dimensões em mm:

