



EcoBATTEN

TMS942 2xTL5-50W/840 EB WR

2, TL5, 50 W, 840 neutral white, Electronic, White reflector without louver

EcoBATTEN is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25, 28, 50 or 54 W TL5 fluorescent tube lamps and can be used at heights of between 2.5 and 12 m. Available in five versions with high performance.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	White reflector without louver
Operating and Electrical	
Power Consumption	50 W

Product Data	
Order product name	TMS942 2xTL5-50W/840 EB WR
Full product name	TMS942 2xTL5-50W/840 EB WR
Full product code	919106031471
Order code	919106031471
Material Nr. (12NC)	919106031471
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

Dimensões em mm:

