



# EcoBATTEN

## TMS943 2XTL5-50W/840 HFD C-H

2, TL5, 50 W, 840 neutral white, HF DALI, High-gloss high reflectance

EcoBATTEN is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25, 28, 50 or 54 W TL5 fluorescent tube lamps and can be used at heights of between 2.5 and 12 m. Available in five versions with high performance.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFD [HF DALI]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	High-gloss high reflectance
Operating and Electrical	
Power Consumption	50 W

Product Data	
Order product name	TMS943 2XTL5-50W/840 HFD C-H
Full product name	TMS943 2XTL5-50W/840 HFD C-H
Full product code	919106031489
Order code	919106031489
Material Nr. (12NC)	919106031489
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400818869
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400818869

Dimensional drawing

Dimensões em mm:

