



EcoBATTEN

TMS944 2xTL5-50W/840 EB D/I WR

2, TL5, 50 W, 840 neutral white, Electronic, White reflector without louver

EcoBATTEN is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25, 28, 50 or 54 W TL5 fluorescent tube lamps and can be used at heights of between 2.5 and 12 m. Available in five versions with high performance.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	White reflector without louver
Operating and Electrical	
Power Consumption	50 W

Product Data	
Order product name	TMS944 2xTL5-50W/840 EB D/I WR
Full product name	TMS944 2xTL5-50W/840 EB D/I WR
Full product code	919106031491
Order code	919106031491
Material Nr. (12NC)	919106031491
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400001858
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400001858

Dimensional drawing

Dimensões em mm:

