



# TCW060 A

## TCW060 2xTL5-54W/840 EB ABS-PC-L

2, TL5, 54 W, 840 neutral white, Electronic, Polycarbonate large

The new TCW060 hermetic luminaire is ideal for use in harsh environments where protection against vapor, water, and dust is required. It has been specially designed and developed for use with TL-D / TL5 tubular fluorescent lamps and electronic ballasts. Its compact and economical design provides perfect integration with the environment. The IP65 protection means the TCW060 is waterproof, enabling it to be used in damp places such as in industry, warehouses, garages, etc. It is easy to install and maintain because it has adjustable ceiling clips to make installation even more flexible and practical.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optical cover type	Polycarbonate large
Operating and Electrical	
Power Consumption	54 W

Product Data	
Order product name	TCW060 2xTL5-54W/840 EB ABS-PC-L
Full product name	TCW060 2xTL5-54W/840 EB ABS-PC-L
Full product code	919106031591
Order code	919106031591
Material Nr. (12NC)	919106031591
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

TCW060 A

Dimensional drawing

