



# TCW060 A

## TCW060 2xTL5-50W/840 EB PC-S

2, TL5, 50 W, 840 neutral white, Electronic, Polycarbonate small

The new TCW060 hermetic luminaire is ideal for use in harsh environments where protection against vapor, water, and dust is required. It has been specially designed and developed for use with TL-D / TL5 tubular fluorescent lamps and electronic ballasts. Its compact and economical design provides perfect integration with the environment. The IP65 protection means the TCW060 is waterproof, enabling it to be used in damp places such as in industry, warehouses, garages, etc. It is easy to install and maintain because it has adjustable ceiling clips to make installation even more flexible and practical.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optical cover type	Polycarbonate small
Operating and Electrical	
Power Consumption	50 W

Product Data	
Order product name	TCW060 2xTL5-50W/840 EB PC-S
Full product name	TCW060 2xTL5-50W/840 EB PC-S
Full product code	919106031691
Order code	919106031691
Material Nr. (12NC)	919106031691
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400001209
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400001209

TCW060 A

Dimensional drawing

