



# TBS065

## TBS065 4XTL-D16W/840 EB C4

4, MASTER TL-D, 16 W, 840 neutral white, Electronic, High-gloss optic with V-shaped cross-lamellae

The TBS065 luminaires were specially developed for indoor commercial lighting, and are available in recessed (TBS065) and surface-mounted (TCS065) models. This is an economical range for use with tubular fluorescent lamps of 16, 20, 32 or 40 W. The TBS can be recessed in any type of ceiling (plaster or paneled) and has a C4 optical system that guarantees high-quality projects, energy savings, excellent lighting efficiency, and easy installation.

### Product data


General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EB [Electronic]
Light Technical	
Number of light sources	4
Light source color	840 neutral white
Optic type	High-gloss optic with V-shaped cross-lamellae
Operating and Electrical	
Power Consumption	16 W

Product Data	
Order product name	TBS065 4XTL-D16W/840 EB C4
Full product name	TBS065 4XTL-D16W/840 EB C4
Full product code	919106031861
Order code	919106031861
Material Nr. (12NC)	919106031861
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400001100
Numerator - Packs per outer box	2
EAN/UPC - Case	7894400001100

TBS065

Dimensional drawing

Dimensões em mm - TBS065



Versão Vazia	A	B	C	D	E
TBS065 4 x 16W/TLD	622	622	592	592	75
TBS065 2 x 32W/TLD	1245	310	1217	280	75

