



# TBS022

## TBS022 2XTL5-50W/840 HFD R-H

2, TL5, 50 W, 840 neutral white, HF DALI, Reflector high reflectance

The TBS022 luminaire has a high-reflectance, high-gloss aluminum reflector. This guarantees high performance, making this system the best lighting solution for retail applications. It also features excellent light distribution, elegance, and advanced technology. This recessed luminaire consists of two TL5 lamps of 50 and 54 W and can be used to replace systems with luminaires for HO 110 W lamps. The high-performance electronic ballast ensures a longer lamp life and is internally mounted in the luminaire, preventing any risk of the wiring being accidentally disconnected during installation.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFD [HF DALI]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	Reflector high reflectance
Operating and Electrical	
Power Consumption	50 W

Product Data	
Order product name	TBS022 2XTL5-50W/840 HFD R-H
Full product name	TBS022 2XTL5-50W/840 HFD R-H
Full product code	919106032164
Order code	919106032164
Material Nr. (12NC)	919106032164
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400819088
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400819088

## TBS022

### Dimensional drawing

