



TCW060 A

TCW060 2XTL-D32W-CO-25 EB110/220V ABS-PC

2, MASTER TL-D, 32 W, 25 neutral white, Electronic, 110 to 220 V, Polycarbonate bowl/cover

The new TCW060 hermetic luminaire is ideal for use in harsh environments where protection against vapor, water, and dust is required. It has been specially designed and developed for use with TL-D / TL5 tubular fluorescent lamps and electronic ballasts. Its compact and economical design provides perfect integration with the environment. The IP65 protection means the TCW060 is waterproof, enabling it to be used in damp places such as in industry, warehouses, garages, etc. It is easy to install and maintain because it has adjustable ceiling clips to make installation even more flexible and practical.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	25 neutral white
Optical cover type	Polycarbonate bowl/cover
Operating and Electrical	
Input Voltage	110 to 220 V
Power Consumption	32 W

Product Data	
Order product name	TCW060 2XTL-D32W-CO-25 EB110/220V ABS-PC
Full product name	TCW060 2XTL-D32W-CO-25 EB110/220V ABS-PC
Full product code	919106032421
Order code	919106032421
Material Nr. (12NC)	919106032421
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400818012
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400818012

TCW060 A

Dimensional drawing

