



EcoBATTEN

TMS943 2XTL5-73W/840 EB R-H

2, TL5, 73 W, 840 neutral white, Electronic, Reflector high reflectance

EcoBATTEN is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25, 28, 50 or 54 W TL5 fluorescent tube lamps and can be used at heights of between 2.5 and 12 m. Available in five versions with high performance.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	Reflector high reflectance
Operating and Electrical	
Power Consumption	73 W

Product Data	
Order product name	TMS943 2XTL5-73W/840 EB R-H
Full product name	TMS943 2XTL5-73W/840 EB R-H
Full product code	919106032431
Order code	919106032431
Material Nr. (12NC)	919106032431
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400818739
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400818739

Dimensional drawing

Dimensões em mm:

