



# ProLux TPS550 A

## TPS550 6×TL5-50W/840 HFD C-H NB

6, TL5, 50 W, 840 neutral white, HF DALI, Narrow beam

Light your factory or work area with the Philips ProLux lighting system, which delivers up to 45% energy savings. The Philips ProLux high-bay solution is a direct replacement for HID high-bay solutions that enables significant energy savings. The combination of robust housing, aluminum reflector with high reflectance (95%) and a specially designed reflector makes this high-efficiency luminaire a more profitable option thanks to its improved energy efficiency. The luminaire's three beam apertures make life easier for the lighting designer and enable a wider range of applications.

### Product data

| General Information      |                   |
|--------------------------|-------------------|
| Lamp family code         | TL5 [TL5]         |
| Gear                     | HFD [HF DALI]     |
| Light Technical          |                   |
| Number of light sources  | 6                 |
| Light source color       | 840 neutral white |
| Optic type               | Narrow beam       |
| Operating and Electrical |                   |
| Power Consumption        | 50 W              |

| Product Data                    |                                 |
|---------------------------------|---------------------------------|
| Order product name              | TPS550 6×TL5-50W/840 HFD C-H NB |
| Full product name               | TPS550 6×TL5-50W/840 HFD C-H NB |
| Full product code               | 919106032501                    |
| Order code                      | 919106032501                    |
| Material Nr. (12NC)             | 919106032501                    |
| Numerator - Quantity Per Pack   | 1                               |
| EAN/UPC - Product/Case          | 7894400818135                   |
| Numerator - Packs per outer box | 1                               |
| EAN/UPC - Case                  | 7894400818135                   |

## ProLux TPS550 A

### Dimensional drawing

