



# ProLux TPS550 A

## TPS550 4×TL5-50W/840 HFD C-H MB

4, TL5, 50 W, 840 neutral white, HF DALI, Medium beam

Light your factory or work area with the Philips ProLux lighting system, which delivers up to 45% energy savings. The Philips ProLux high-bay solution is a direct replacement for HID high-bay solutions that enables significant energy savings. The combination of robust housing, aluminum reflector with high reflectance (95%) and a specially designed reflector makes this high-efficiency luminaire a more profitable option thanks to its improved energy efficiency. The luminaire's three beam apertures make life easier for the lighting designer and enable a wider range of applications.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFD [HF DALI]
Light Technical	
Number of light sources	4
Light source color	840 neutral white
Optic type	Medium beam
Operating and Electrical	
Power Consumption	50 W

Product Data	
Order product name	TPS550 4×TL5-50W/840 HFD C-H MB
Full product name	TPS550 4×TL5-50W/840 HFD C-H MB
Full product code	919106032541
Order code	919106032541
Material Nr. (12NC)	919106032541
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400818173
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400818173

## ProLux TPS550 A

### Dimensional drawing

