



TCS165 A

TCS165 3XTL5-13W/840 EB C6

3, TL5, 13 W, 840 neutral white, Electronic, High-gloss optic double parabolic closed

Designed to meet the need for energy-efficient lighting, the TCS165 luminaire incorporates Philips TL5 technology, which means it saves on energy and is ideal for replacing outdated facilities. With its innovative design and dedicated optics, the TCS165 range can be used as general lighting in a wide variety of applications including offices, corridors, schools, and shops (supermarkets, DIY). Used in combination with electronics ballasts and Philips TL5 lamps, it provides substantial energy savings. The low-height luminaire is ideal when the distance between the ceiling and the slab is limited. For greater convenience, the luminaire does not have to be opened because it has pre-installed lamps and can be connected from the outside.

Product data

| General Information | |
|--------------------------|--|
| Lamp family code | TL5 [TL5] |
| Gear | EB [Electronic] |
| Light Technical | |
| Number of light sources | 3 |
| Light source color | 840 neutral white |
| Optic type | High-gloss optic double parabolic closed |
| Operating and Electrical | |
| Power Consumption | 13 W |

| Product Data | |
|---------------------------------|----------------------------|
| Order product name | TCS165 3XTL5-13W/840 EB C6 |
| Full product name | TCS165 3XTL5-13W/840 EB C6 |
| Full product code | 919106032601 |
| Order code | 919106032601 |
| Material Nr. (12NC) | 919106032601 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 7894400818524 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 7894400818524 |

TCS165 A

Dimensional drawing

