



Image  
not yet  
available

# TCS165 A

## TCS165 2XTL5-50W/840 HFD C6

2, TL5, 50 W, 840 neutral white, HF DALI, High-gloss optic double parabolic closed

Designed to meet the need for energy-efficient lighting, the TCS165 luminaire incorporates Philips TL5 technology, which means it saves on energy and is ideal for replacing outdated facilities. With its innovative design and dedicated optics, the TCS165 range can be used as general lighting in a wide variety of applications including offices, corridors, schools, and shops (supermarkets, DIY). Used in combination with electronics ballasts and Philips TL5 lamps, it provides substantial energy savings. The low-height luminaire is ideal when the distance between the ceiling and the slab is limited. For greater convenience, the luminaire does not have to be opened because it has pre-installed lamps and can be connected from the outside.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFD [HF DALI]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	High-gloss optic double parabolic closed
Operating and Electrical	
Power Consumption	50 W

Product Data	
Order product name	TCS165 2XTL5-50W/840 HFD C6
Full product name	TCS165 2XTL5-50W/840 HFD C6
Full product code	919106032661
Order code	919106032661
Material Nr. (12NC)	919106032661
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400818555
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400818555

Dimensional drawing

