



# SmartLED Waterproof BCW060 A

## BCW060 2XMLED-TL-22W/840 100-240V PC-L

2, MASTER LED, 22 W, 840 neutral white, 100 to 240 V,  
Polycarbonate large

### Product data

General Information	
Lamp family code	LED [MASTER LED]
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optical cover type	Polycarbonate large
Operating and Electrical	
Input Voltage	100 to 240 V
Power Consumption	22 W

Application Conditions	
Performance ambient temperature	25 °C
Tq	
Product Data	
Order product name	BCW060 2XMLED-TL-22W/840 100-240V PC-L
Full product name	BCW060 2XMLED-TL-22W/840 100-240V PC-L
Full product code	919106032681
Order code	919106032681
Material Nr. (12NC)	919106032681
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400818609
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400818609

## SmartLED Waterproof BCW060 A

### Dimensional drawing

#### Dimensões em mm:

