



SlimLine TCS020

TCS020 2xTL5-25W/840 EB C5

2, TL5, 25 W, 840 neutral white, Electronic, High-gloss optic double parabolic

SlimLine luminaires are compact and versatile to allow better distribution of light in the environment. Their slim design offers lots of advantages to designers and installers, with better adaptation to ceilings. Available in recessed (TBS020) and surface-mounted (TCS020) models with a choice of four optical systems. Ideal for 16 and 32 W TL-D tubular fluorescent lamps.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	High-gloss optic double parabolic
Optical cover type	-
Operating and Electrical	
Power Consumption	25 W

Product Data	
Order product name	TCS020 2xTL5-25W/840 EB C5
Full product name	TCS020 2xTL5-25W/840 EB C5
Full product code	919106032731
Order code	919106032731
Material Nr. (12NC)	919106032731
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400818678
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400818678

SlimLine TCS020

Dimensional drawing

