



# SlimLine TCS020

## TCS020 2xTL5-50W/840 EB C1

2, TL5, 50 W, 840 neutral white, Electronic, High-gloss mirror flat lamellae louver

SlimLine luminaires are compact and versatile to allow better distribution of light in the environment. Their slim design offers lots of advantages to designers and installers, with better adaptation to ceilings. Available in recessed (TBS020) and surface-mounted (TCS020) models with a choice of four optical systems. Ideal for 16 and 32 W TL-D tubular fluorescent lamps.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	High-gloss mirror flat lamellae louver
Optical cover type	-
Operating and Electrical	
Power Consumption	50 W

Product Data	
Order product name	TCS020 2xTL5-50W/840 EB C1
Full product name	TCS020 2xTL5-50W/840 EB C1
Full product code	919106032761
Order code	919106032761
Material Nr. (12NC)	919106032761
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400818715
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400818715

# SlimLine TCS020

## Dimensional drawing

Dimensões em mm:

Sobrepor (TCS 020)

