



SlimLine TBS020

TBS020 2XTL5-25W/840 EB AC

2, TL5, 25 W, 840 neutral white, Electronic, Acrylic bowl/cover

SlimLine luminaires are compact and versatile for better distribution of light in the environment. Their slim design offers lots of advantages to designers and installers, with better adaptation to ceilings. Available in recessed (TBS020) and surface-mounted (TCS020) models with a choice of four optical systems. Ideal for 16 and 32 W TL-D tubular fluorescent lamps.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	-
Optical cover type	Acrylic bowl/cover
Operating and Electrical	
Power Consumption	25 W

Product Data	
Order product name	TBS020 2XTL5-25W/840 EB AC
Full product name	TBS020 2XTL5-25W/840 EB AC
Full product code	919106032781
Order code	919106032781
Material Nr. (12NC)	919106032781
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400818708
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400818708

SlimLine TBS020

Dimensional drawing

