



TBS165 A

TBS165 4XTL5-13W/840 HFD C6

4, TL5, 13 W, 840 neutral white, HF DALI, High-gloss optic double parabolic closed

Designed to meet the need for energy-efficient lighting, the TBS165 luminaire incorporates Philips TL5 technology, which means it saves on energy and is ideal for replacing outdated facilities. With its innovative design and dedicated optics, the TBS165 range can be applied as general lighting in a wide variety of applications including offices, corridors, schools, and shops (supermarkets, DIY). Used in combination with electronic ballasts and Philips TL5 lamps, it provides substantial energy savings. The low-height luminaire is ideal when the distance between the ceiling and the slab is limited. For greater convenience, the luminaire does not have to be opened because it has pre-installed lamps and can be connected from the outside.

Product data

General Information		Product Data	
Lamp family code	TL5 [TL5]	Order product name	TBS165 4XTL5-13W/840 HFD C6
Gear	HFD [HF DALI]	Full product name	TBS165 4XTL5-13W/840 HFD C6
Light Technical		Full product code	919106032851
Number of light sources	4	Order code	919106032851
Light source color	840 neutral white	Material Nr. (12NC)	919106032851
Optic type	High-gloss optic double parabolic closed	Numerator - Quantity Per Pack	1
Operating and Electrical		EAN/UPC - Product/Case	7894400000622
Power Consumption	13 W	Numerator - Packs per outer box	1
		EAN/UPC - Case	7894400000622

TBS165 A

Dimensional drawing

