



TBS027

TBS027 2XTL-D32W/840 EI 110/220V R-H

2, MASTER TL-D, 32 W, 840 neutral white, Electronic Included, 110 to 220 V, Reflector high reflectance

The TBS027 luminaires have a compact design for use in areas that require diffuse light in large quantities. The recessed models are designed for use with 32 W TL-D tubular fluorescent lamps and are easy to install and maintain. Also available for surface mounting (TCS027).

Product data

| General Information | |
|--------------------------|----------------------------|
| Lamp family code | TL-D [MASTER TL-D] |
| Gear | EI [Electronic Included] |
| Light Technical | |
| Number of light sources | 2 |
| Light source color | 840 neutral white |
| Optic type | Reflector high reflectance |
| Operating and Electrical | |
| Input Voltage | 110 to 220 V |
| Power Consumption | 32 W |

| Product Data | |
|---------------------------------|--------------------------------------|
| Order product name | TBS027 2XTL-D32W/840 EI 110/220V R-H |
| Full product name | TBS027 2XTL-D32W/840 EI 110/220V R-H |
| Full product code | 919106050091 |
| Order code | 919106050091 |
| Material Nr. (12NC) | 919106050091 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

TBS027

Dimensional drawing

Dimensões em mm:

