



TCS027

TCS027 2XTL-D32W/840 EB R-H

2, MASTER TL-D, 32 W, 840 neutral white, Electronic, Reflector high reflectance

The TCS027 luminaires have a compact design for use in areas that require diffuse light in large quantities. The surface-mounted models are designed for use with 32 W TL-D tubular fluorescent lamps and are easy to install and maintain. Also available for recessed mounting (TBS027).

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	Reflector high reflectance
Operating and Electrical	
Power Consumption	32 W

Product Data	
Order product name	TCS027 2XTL-D32W/840 EB R-H
Full product name	TCS027 2XTL-D32W/840 EB R-H
Full product code	919106050131
Order code	919106050131
Material Nr. (12NC)	919106050131
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

TCS027

Dimensional drawing

Dimensões em mm:

