



DBG

DBG110 1xCDM-R30-30-35W/830 EB WH

1, MASTERColour CDM-R PAR-30, 30 degree(s), 35 W, 830 warm white, Electronic, White

The DBG range creates an inviting, comfortable and distinctive atmosphere, so the lighting serves as an excellent way to promote sales. Perfect accompaniment for the latest trends in interior architecture.


Product data

General Information	
Lamp family code	CDM-R30 [MASTERColour CDM-R PAR-30]
Gear	EB [Electronic]
Light Technical	
Number of light sources	1
Beam angle of light source	30 degree(s)
Light source color	830 warm white
Operating and Electrical	
Power Consumption	35 W
Mechanical and Housing	
Housing Color	White

Product Data	
Order product name	DBG110 1xCDM-R30-30-35W/830 EB WH
Full product name	DBG110 1xCDM-R30-30-35W/830 EB WH
Full product code	919206004439
Order code	919206004439
Material Nr. (12NC)	919206004439
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

DBG

Dimensional drawing



Dimensões em mm

