



ConTempo

152-252-352

RVP252 MHN-TD150W/842 220V-60Hz S

MHN-TD, 150 W, Symmetrical

The Contempo projector has a highly innovative design. It is made of cast aluminum with a powder coating, which makes it more robust for use outdoors. It has a dedicated housing for auxiliary equipment (ballast, igniter and capacitor), mounted on an aluminum chassis, which ensures excellent heat dissipation.


Product data

| General Information | |
|--------------------------|-------------------|
| Lamp family code | MHN-TD |
| Light Technical | |
| Light source color | 842 neutral white |
| Optic type outdoor | Symmetrical |
| Operating and Electrical | |
| Input Voltage | 220 V |
| Line Frequency | 60 Hz |
| Power Consumption | 150 W |

| Product Data | |
|---------------------------------|-----------------------------------|
| Order product name | RVP252 MHN-TD150W/842 220V-60Hz S |
| Full product name | RVP252 MHN-TD150W/842 220V-60Hz S |
| Full product code | 919306012995 |
| Order code | 919306012995 |
| Material Nr. (12NC) | 919306012995 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 7894400003272 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 7894400003272 |

Dimensional drawing

Dimensional drawing



Adjustment possibilities

