



# MDW502/503

## MDW502 HPI-P250W-BU K 220V-60Hz R WB

MASTER HPI Plus, 250 W, 220 V, 60 Hz, Reflector wide beam

Industrial luminaire for damp environments where protection against gases, vapors and dust is needed. Designed using high-quality materials, its optical system is composed of high-purity spun and anodized aluminum with a high lighting performance. Ideal for use with SON sodium vapor lamps or HPI-BU metal-halide lamps of 250 to 400 W. Reflectors are available in two versions: open beam for heights between 6 and 9 meters (MDW 503) and closed beam for heights above 9 meters (MDW 502). Easy to install with support hook, has protective glass housing for auxiliary equipment.

### Product data

General Information	
Lamp family code	HPI-P [MASTER HPI Plus]
Light Technical	
Optic type	Reflector wide beam
Operating and Electrical	
Input Voltage	220 V
Line Frequency	60 Hz
Power Consumption	250 W
Product Data	
Order product name	MDW502 HPI-P250W-BU K 220V-60Hz R WB

Full product name	MDW502 HPI-P250W-BU K 220V-60Hz R WB
Full product code	919306015561
Order code	919306015561
Material Nr. (12NC)	919306015561
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400811419
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400811419

## MDW502/503

### Dimensional drawing

Dimensões em mm:

