



# MDW502/503

## MDW503 HPI-P400W-BU K 220V-60Hz R NB

MASTER HPI Plus, 400 W, 220 V, 60 Hz, Reflector narrow beam

Industrial luminaire for damp environments where protection against gases, vapors and dust is needed. Designed using high-quality materials, its optical system is composed of high-purity spun and anodized aluminum with a high lighting performance. Ideal for use with SON sodium vapor lamps or HPI-BU metal-halide lamps of 250 to 400 W. Reflectors are available in two versions: open beam for heights between 6 and 9 meters (MDW 503) and closed beam for heights above 9 meters (MDW 502). Easy to install with support hook, has protective glass housing for auxiliary equipment.

### Product data

General Information	
Lamp family code	HPI-P [MASTER HPI Plus]
Light Technical	
Optic type	Reflector narrow beam
Operating and Electrical	
Input Voltage	220 V
Line Frequency	60 Hz
Power Consumption	400 W
Product Data	
Order product name	MDW503 HPI-P400W-BU K 220V-60Hz R NB

Full product name	MDW503 HPI-P400W-BU K 220V-60Hz R NB
Full product code	919306015611
Order code	919306015611
Material Nr. (12NC)	919306015611
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400811488
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400811488

## MDW502/503

### Dimensional drawing

Dimensões em mm:

