



GreenAccent

RS181B A LED10/830 PSU-E NB 16G WH

LED Module 1000 lm, 830 warm white, Power supply unit external (On/Off), Narrow beam, White

The new GreenAccent LED accent luminaire has a refined finish, and the 4 different mounting options make it possible to address an environment's accent lighting needs while retaining the same visual concept. With optimized service life in the segment and high energy efficiency, it allows the replacement of traditional metal vapor lamp systems with high quality lighting and faithful color rendering.

Product data

General Information		Mechanical and Housing	
Lamp family code	LED10 [LED Module 1000 lm]	Housing Color	White
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Application Conditions	
		Performance ambient temperature	25 °C
		Tq	
Light Technical		Product Data	
Number of light sources	1	Order product name	RS181B A LED10/830 PSU-E NB 16G WH
Light source color	830 warm white	Order code	919406000601
Optic type	Narrow beam	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	919406000601
		Full product name	RS181B A LED10/830 PSU-E NB 16G WH
Controls and Dimming			
Driver/power unit/transformer	Power supply unit external (On/Off)		