



GreenAccent

ST181T A LED20/830 PSU-E NB 16G 1C WH

LED Module 2000 lm, 830 warm white, Power supply unit external (On/Off), Narrow beam, White

The new GreenAccent LED accent luminaire has a refined finish, and the 4 different mounting options make it possible to address an environment's accent lighting needs while retaining the same visual concept. With optimized service life in the segment and high energy efficiency, it allows the replacement of traditional metal vapor lamp systems with high quality lighting and faithful color rendering.

Product data

General Information		Mechanical and Housing	
Lamp family code	LED20 [LED Module 2000 lm]	Housing Color	White
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Application Conditions	
Light Technical		Performance ambient temperature	25 °C
Number of light sources	1	Tq	
Light source color	830 warm white	Product Data	
Optic type	Narrow beam	Order product name	ST181T A LED20/830 PSU-E NB 16G 1C WH
Controls and Dimming		Order code	919406000811
Driver/power unit/transformer	Power supply unit external (On/Off)	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	919406000811
		Full product name	ST181T A LED20/830 PSU-E NB 16G 1C WH