



# D'ECO Light Collection

## FBS320/321/323/331

### FBS320 2XPL-C/4P26W/840 EB GF WH

2, MASTER PL-C 4 Pin, 26 W, Electronic, Glass frosted

The D'ECO Light Collection range offers distinctive design and a wide variety of models and formats. With a compact and discreet design, it maintains the same consistent look throughout the range and offers several optical system options, from glass to anti-glare shades. Easy to install and highly flexible, it can be adjusted to accommodate different-sized lamps with the same luminaire.

#### Product data

General Information		Mechanical and Housing	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]	Housing Color	White
Gear	EB [Electronic]		
Light Technical		Product Data	
Number of light sources	2	Order product name	FBS320 2XPL-C/4P26W/840 EB GF WH
Light source color	840 neutral white	Full product name	FBS320 2XPL-C/4P26W/840 EB GF WH
Optical cover type	Glass frosted	Full product code	919406003891
		Order code	919406003891
		Material Nr. (12NC)	919406003891
Operating and Electrical		Numerator - Quantity Per Pack	1
Input Voltage	220 V	Numerator - Packs per outer box	1
Line Frequency	60 Hz		
Input Frequency	60 Hz		
Power Consumption	26 W		

## D'ECO Light Collection FBS320/321/323/331

### Dimensional drawing

