



D'ECO Light Collection

FBS320/321/323/331

FBS321 2XPL-C/4P26W/840 EB GF WH

2, MASTER PL-C 4 Pin, 26 W, 840 neutral white, Electronic, Glass frosted, White

The D'ECO Light Collection range offers distinctive design and a wide variety of models and formats. With a compact and discreet design, it maintains the same consistent look throughout the range and offers several optical system options, from glass to anti-glare shades. Easy to install and highly flexible, it can be adjusted to accommodate different-sized lamps with the same luminaire.

Product data

General Information		Power Consumption	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]	26 W	
Gear	EB [Electronic]		
Light Technical		Mechanical and Housing	
Number of light sources	2	Housing Color	
Light source color	840 neutral white	White	
Optical cover type	Glass frosted		
Operating and Electrical		Product Data	
Input Voltage	220 V	Order product name	
Line Frequency	60 Hz	FBS321 2XPL-C/4P26W/840 EB GF WH	
		Full product name	
		FBS321 2XPL-C/4P26W/840 EB GF WH	
		Full product code	
		919406003991	
		Order code	
		919406003991	
		Material Nr. (12NC)	
		919406003991	
		Numerator - Quantity Per Pack	
		1	
		EAN/UPC - Product/Case	
		7894400002367	

D'ECO Light Collection FBS320/321/323/331

Numerator - Packs per outer box	1
EAN/UPC - Case	7894400002367

Dimensional drawing

