



# D'ECO Light Collection

## FBS320/321/323/331

### FBS323 2xPL-C/4P32W/840 EB WH

2, MASTER PL-T 4 Pin, 32 W, 840 neutral white, Electronic, White

The D'ECO Light Collection range offers distinctive design and a wide variety of models and formats. With a compact and discreet design, it maintains the same consistent look throughout the range and offers several optical system options, from glass to anti-glare shades. Easy to install and highly flexible, it can be adjusted to accommodate different-sized lamps with the same luminaire.

#### Product data

<b>General Information</b>		<b>Power Consumption</b>	
Lamp family code	PL-T/4P [MASTER PL-T 4 Pin]		32 W
Gear	EB [Electronic]	<b>Mechanical and Housing</b>	
<b>Light Technical</b>		Housing Color	White
Number of light sources	2	<b>Product Data</b>	
Light source color	840 neutral white	Order product name	FBS323 2xPL-C/4P32W/840 EB WH
<b>Operating and Electrical</b>		Full product name	FBS323 2xPL-C/4P32W/840 EB WH
Input Voltage	220 V	Full product code	919406004251
Line Frequency	60 Hz	Order code	919406004251
Input Frequency	60 Hz	Material Nr. (12NC)	919406004251
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1

## D'ECO Light Collection FBS320/321/323/331

---

### Dimensional drawing

