



# D'ECO Light Collection

## FBS320/321/323/331

### FBS331 2XPL-T/4P32W/840 EB GF WH

2, MASTER PL-T 4 Pin, 32 W, 840 neutral white, Electronic, Glass frosted, White

The D'ECO Light Collection range offers distinctive design and a wide variety of models and formats. With a compact and discreet design, it maintains the same consistent look throughout the range and offers several optical system options, from glass to anti-glare shades. Easy to install and highly flexible, it can be adjusted to accommodate different-sized lamps with the same luminaire.

#### Product data

General Information	
Lamp family code	PL-T/4P [MASTER PL-T 4 Pin]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optical cover type	Glass frosted
Operating and Electrical	
Power Consumption	32 W
Mechanical and Housing	
Housing Color	White

Product Data	
Order product name	FBS331 2XPL-T/4P32W/840 EB GF WH
Full product name	FBS331 2XPL-T/4P32W/840 EB GF WH
Full product code	919406004351
Order code	919406004351
Material Nr. (12NC)	919406004351
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## D'ECO Light Collection FBS320/321/323/331

### Dimensional drawing

