



# D'ECO Light Collection FCS321

## FCS321 2XPL-C/4P26W/840 EB GF WH

2, MASTER PL-C 4 Pin, 26 W, 840 neutral white, Glass frosted, White

The D'ECO Light Collection range offers distinctive design and a wide variety of models and formats. With a compact and discreet design it maintains the same consistent look throughout the range and offers several optical system options, from glass to anti-glare shades. Easy to install and highly flexible, it can be adjusted to accommodate different-sized lamps with the same luminaire.

### Product data

General Information	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optical cover type	Glass frosted
Operating and Electrical	
Input Voltage	220 V
Line Frequency	60 Hz
Power Consumption	26 W
Mechanical and Housing	
Housing Color	White

Product Data	
Order product name	FCS321 2XPL-C/4P26W/840 EB GF WH
Full product name	FCS321 2XPL-C/4P26W/840 EB GF WH
Full product code	919406004981
Order code	919406004981
Material Nr. (12NC)	919406004981
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400002428
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400002428

## D'ECO Light Collection FCS321

### Dimensional drawing

