



SoftLED Recessed BBS262

BBS262 LED45/840 PSD ACO SQR WH

LED Module 4500 lm, 840 neutral white, Power supply unit with DALI interface, Acrylic bowl/cover opal, White

Philip's new SoftLED light fitting is an innovative lighting solution. The highly efficient LEDs offer huge energy savings and the design of the opaque acrylic diffuser ensures perfect, comfortable distribution of the light. The elegant, discreet installation is available in square and rectangular designs, and the DALI dimmer-controlled version is perfect for use with an integrated lighting control system.

Product data

General Information		Controls and Dimming	
Lamp family code	LED45 [LED Module 4500 lm]	Driver/power unit/transformer	Power supply unit with DALI interface
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Mechanical and Housing	
Light Technical		Housing Color	White
Correlated Color Temperature (Nom)		Application Conditions	
4000 K		Performance ambient temperature	25 °C
Light source color		Tq	
Optical cover type		Product Data	
Acrylic bowl/cover opal		Order product name	BBS262 LED45/840 PSD ACO SQR WH
		Full product name	BBS262 LED45/840 PSD ACO SQR WH
		Full product code	919406016471
		Order code	919406016471
		Material Nr. (12NC)	919406016471

SoftLED Recessed BBS262

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400000028
Numerator - Packs per outer box	1

EAN/UPC - Case	7894400000028
----------------	---------------

