



# HDK472/473/474

## HDK474 E40 MAX400W

E40

This modular range of high-bay industrial HDK luminaires is ideal for use in large indoor areas and is designed to work with 250 or 400 W sodium, metal-halide or mercury vapor lamps. Produced with high-quality materials, it offers two reflector options: open (GDK472) or closed (GDK473), and may be accompanied with a glass front (GDK472 PG or GDK473 PG), depending on the reflector. The HDK472/473 model features a tube suspension system (ZDK472 SPR), or track/rail (ZDKEH 473). The HDK474 model is made of cast aluminum, for use without ballast housing.

### Product data

|                                 |                    |
|---------------------------------|--------------------|
| <b>General Information</b>      |                    |
| Cap-Base                        | E40 [E40]          |
| <b>Operating and Electrical</b> |                    |
| Input Voltage                   | 220 V              |
| Line Frequency                  | 60 Hz              |
| <b>Product Data</b>             |                    |
| Order product name              | HDK474 E40 MAX400W |

|                                 |                    |
|---------------------------------|--------------------|
| Full product name               | HDK474 E40 MAX400W |
| Full product code               | 919506002651       |
| Order code                      | 919506002651       |
| Material Nr. (12NC)             | 919506002651       |
| Numerator - Quantity Per Pack   | 1                  |
| Numerator - Packs per outer box | 10                 |

HDK472/473/474

Dimensional drawing

