



MDK500

MDK500 HPI-P250W-BU 220V-60HZ

MASTER HPI Plus, 250 W, 220 V, 60 Hz

The MDK luminaire is ideal for use in large indoor areas and provides three-dimensional lighting with an excellent level of illumination in the vertical and horizontal planes. The acrylic diffuser creates an environment free of glare and shadows, ensuring greater visual comfort. It includes a housing for ancillary equipment, and a clear acrylic diffuser for 250 or 400 W metal-halide and sodium vapor lamps. It has a hook for support and an aluminum box for heat dissipation.

Product data

General Information	
Lamp family code	HPI-P [MASTER HPI Plus]
Operating and Electrical	
Input Voltage	220 V
Line Frequency	60 Hz
Power Consumption	250 W
Product Data	
Order product name	MDK500 HPI-P250W-BU 220V-60HZ

Full product name	MDK500 HPI-P250W-BU 220V-60HZ
Full product code	919506005351
Order code	919506005351
Material Nr. (12NC)	919506005351
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

MDK500

Dimensional drawing

Dimensões em mm:

