



MDK500

GDK500 HPI-P250W-BU K PR-AC

The MDK luminaire is ideal for use in large indoor areas and provides three-dimensional lighting with an excellent level of illumination in the vertical and horizontal planes. The acrylic diffuser creates an environment free of glare and shadows, ensuring greater visual comfort. It includes a housing for ancillary equipment, and a clear acrylic diffuser for 250 or 400 W metal-halide and sodium vapor lamps. It has a hook for support and an aluminum box for heat dissipation.

Product data

General Information		Full product code		919506006321
Lamp family code	HPI-P [MASTER HPI Plus]	Order code	919506006321	
Operating and Electrical		Material Nr. (12NC)	919506006321	
Power Consumption	250 W	Numerator - Quantity Per Pack	1	
Product Data		EAN/UPC - Product/Case	7894400001575	
Order product name	GDK500 HPI-P250W-BU K PR-AC	Numerator - Packs per outer box	7	
Full product name	GDK500 HPI-P250W-BU K PR-AC	EAN/UPC - Case	7894400001575	