



# MDK500

## GDK500 HPI-P400W-BU K PR-AC

The MDK luminaire is ideal for use in large indoor areas and provides three-dimensional lighting with an excellent level of illumination in the vertical and horizontal planes. The acrylic diffuser creates an environment free of glare and shadows, ensuring greater visual comfort. It includes a housing for ancillary equipment, and a clear acrylic diffuser for 250 or 400 W metal-halide and sodium vapor lamps. It has a hook for support and an aluminum box for heat dissipation.

### Product data

<b>General Information</b>		<b>Full product code</b>		919506006331
Lamp family code	HPI-P [MASTER HPI Plus]	Order code	919506006331	
<b>Operating and Electrical</b>		Material Nr. (12NC)	919506006331	
Power Consumption	400 W	Numerator - Quantity Per Pack	1	
<b>Product Data</b>		EAN/UPC - Product/Case	7894400001582	
Order product name	GDK500 HPI-P400W-BU K PR-AC	Numerator - Packs per outer box	7	
Full product name	GDK500 HPI-P400W-BU K PR-AC	EAN/UPC - Case	7894400001582	