



Image
not yet
available

ArenaVision Gear EVF403/404

EVF403 A MHN-LA1000W 230V-60Hz SI IP20

MASTER MHN-LA, 1000 W

Ballast and capacitor for installation with the ArenaVision luminaire range. Can be installed in ZVF403/404 box for use in external locations (IP65).

Product data

General Information	
Lamp family code	MHN-LA [MASTER MHN-LA]
Operating and Electrical	
Input Voltage	230 V
Line Frequency	60 Hz
Power Consumption	1,000 W
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	EVF403 A MHN-LA1000W 230V-60Hz SI IP20

Full product name	EVF403 A MHN-LA1000W 230V-60Hz SI IP20
Full product code	919506006861
Order code	919506006861
Material Nr. (12NC)	919506006861
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400003852
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400003852