



MBR/MBS902

ZBR902 GRT HPI-T400W-BU 220V/60HZ

HPI-T High Wattage, 400 W, 220 V, 60 Hz

The MBR/S 902 range has been designed for use in sheltered outdoor areas such as gas stations. Totally protected against dust and insects, it is an excellent choice at a very attractive price.

Product data

General Information	
Lamp family code	HPI-T [HPI-T High Wattage]
Operating and Electrical	
Input Voltage	220 V
Line Frequency	60 Hz
Power Consumption	400 W
Product Data	
Order product name	ZBR902 GRT HPI-T400W-BU 220V/60HZ

Full product name	ZBR902 GRT HPI-T400W-BU 220V/60HZ
Full product code	919506015091
Order code	919506015091
Material Nr. (12NC)	919506015091
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400817343
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400817343