



# MDK500

## GDK500 MAX400W-BU PR-AC

### Acrylic reflector

The MDK luminaire is ideal for use in large indoor areas and provides three-dimensional lighting with an excellent level of illumination in the vertical and horizontal planes. The acrylic diffuser creates an environment free of glare and shadows, ensuring greater visual comfort. It includes a housing for ancillary equipment, and a clear acrylic diffuser for 250 or 400 W metal-halide and sodium vapor lamps. It has a hook for support and an aluminum box for heat dissipation.

### Product data

<b>General Information</b>		<b>Full product code</b>		919506105331
Lamp family code	HPI-P [MASTER HPI Plus]	Order code	919506105331	
<b>Operating and Electrical</b>		Material Nr. (12NC)	919506105331	
<b>Product Data</b>		Numerator - Quantity Per Pack	1	
Power Consumption	400 W	EAN/UPC - Product/Case	7894400001568	
Order product name	GDK500 MAX400W-BU PR-AC	Numerator - Packs per outer box	7	
Full product name	GDK500 MAX400W-BU PR-AC	EAN/UPC - Case	7894400001568	