



SLS1500

MVP128 MH1500W-BU R-NB IP55

Metal Halide MH, 1500 W, Reflector narrow beam

SLS projectors are lightweight and compact. Ideal for outdoor lighting, they are designed for use with 1500 W metal-halide lamps or 1000 W sodium vapor lamps. They are available in two beam apertures: open and closed. A high-gloss aluminum reflector with enclosed glass front provides protection against dust. They are easy to install and deliver excellent lighting performance.

Product data

General Information	
Lamp family code	MH [Metal Halide MH]
Light Technical	
Optic type outdoor	Reflector narrow beam
Operating and Electrical	
Power Consumption	1,500 W
Approval and Application	
Ingress protection code	IP55 [Dust accumulation-protected, jet-proof]

Product Data	
Order product name	MVP128 MH1500W-BU R-NB IP55
Full product name	MVP128 MH1500W-BU R-NB IP55
Full product code	919506110121
Order code	919506110121
Material Nr. (12NC)	919506110121
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400003425
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400003425

SLS1500

Dimensional drawing

Dimensões em mm:

