



## Frost / Clear

### 200A CDA 130V 60PK

The Philips Family of Standard Frost and Clear bulbs are good for everyday use. Clear bulbs provide sparkle, especially in fixtures that are made of chrome, have mirrored surfaces, multiple sockets or have cut glass parts. If glare is a problem, use a dimmer or a lower wattage bulb to reduce brightness. Clear bulbs are also used in fixtures with reflectors. Frost bulbs provide soft light with reduced glare.


#### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	750 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	3,600 lumen
Operating and Electrical	
Power Consumption	200 W
Voltage (Nom)	130 V
Voltage (Nom)	130 V
Mechanical and Housing	
Bulb Finish	Frosted

Bulb Shape	A23 [A 23mm]
Product Data	
Order product name	200A CDA 130V 60PK
Order code	920080836102
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	60
Material Nr. (12NC)	920080836102
Full product name	200A CDA 130V 60PK
EAN/UPC - Case	50046677362916
EAN/UPC - Product/Case	046677362911

Frost / Clear

Dimensional drawing



Product	D	C (max)
200A CDA 130V 60PK	2.625 inch	6.313 inch

